



MULTICOMPOUND GAS ANALYZER

MGA Overview

High-precision all-in-one gas analyzers to combat climate change and air pollution

Innovation with Integrity

Highlights

- Measures 10 gases simultaneously selectable from: **CH₄**, **CO**, **CO₂**, **SO₂**, **NH₃**, **N₂O**, **NO**, **NO₂**, **H₂O**, **O₃**, **OCS**, **HCHO** and **HONO**
- Direct measurement of all compounds (incl. NO₂)
- High precision for ambient air quality and greenhouse gas monitoring at low concentrations
- High time resolution (1 Hz or 10 Hz)
- Suitable for laboratory applications, field deployable and mobile measurements (aircraft, vehicle, marine, ground-based stations)

The MIRO MGA¹⁰-GP has revolutionized and simplified the monitoring of greenhouse gases and air pollutants by enabling simultaneous online measurements of 10 gases at high measurement rates, while offering excellent stability and precision. Different gas combination options are below:

	Gas Species	MGA ¹⁰ - GP				MGA ⁵ - GHG	MGA ³ - GHG		
		C1	C2	C3	C4	C1	C1	C2	C3
GHG	H ₂ O	✓	✓	✓	✓	✓	✓	✓	✓
	CO	✓	✓	✓	✓	✓	-	✓	-
	CO ₂	✓	✓	✓	✓	✓	-	-	✓
	N ₂ O	✓	✓	✓	-	✓	✓	✓	-
	CH ₄	✓	✓	-	✓	✓	✓	-	-
Pollutants	NH ₃	✓	✓	✓	✓	-	-	-	-
	NO	✓	✓	✓	✓	-	-	-	-
	NO ₂	✓	✓	✓	✓	-	-	-	-
	O ₃	✓	✓	✓	✓	-	-	-	-
	OCS	-	✓	✓	✓	-	-	-	✓
	SO ₂	✓	-	-	✓	-	-	-	-
	HONO	-	-	✓	-	-	-	-	-

MIRO's MGA¹⁰-GP analyzers directly measure concentrations of all compounds using mid-infrared laser absorption spectroscopy with **Quantum Cascade Lasers**. This allows for highly specific and accurate gas detection along with maximum measurement sensitivity.

Our analyzers are typically free of measurement interferences from other gas species. The intuitive touch display enables fast and easy control. The analyzer is suitable for various applications from air monitoring to **eddy covariance flux** measurements.

MIRO's products are made in Switzerland and undergo strict quality control before shipping.

Applications

MGA is a general purpose multicomponent gas analyzer suitable for a wide range of applications.

Atmospheric Science



- Direct & precise
- Continuous measurements of most of the regulated/observed atmospheric gases
- Almost no maintenance required

Biosphere




- Field deployable
- Low gas flows possible
- No interference from other gases

Accessories & Options

10 Hz Sampling Rate


An increased flow and sampling rate enables fast measurements as required for eddy covariance.



MIRO Mobile Kit

Shock-proofed rack including a battery to run the system up to 10 h without external power supply. Ideal for airborne, zeppelin-, ship- or car-based mobile measurements.

System Parameters	Specification
Dimensions	94 w x 66 h x 70 d
Rack Weight	29 kg
Total System Weight	109 kg
Battery Capacity	3 kWh
Max. Vertical Acceleration	5 G




MIRO Field Enclosure

Protects the instrument with rugged casing and provides a temperature controlled environment for stable measurements.



Valve Sequencer Option

Adjustable automatic valve sequencer controlling up to 3 external 3 way valves. Ideal for advanced calibration settings.



Eddy Covariance



- Field deployable
- High time resolution (10 Hz)

Mobile Measurements



- Compact & robust
- Shock-proofed
- Lower power consumption
- All-in-one lab

General Technical Specifications

Parameters	1 Hz	10 Hz
Ambient Temperature	15 - 30°C	
Ambient Humidity	< 90% RH, non-condensing	
Sample Pressure	700 - 1050 mbar	
Sample Flow Rate	0.5 to 1.5 slpm	15 slpm
Sample Inlet Fittings	6 mm - Swagelok	12 mm - Swagelok
Dimensions	48 w x 18 h x 70 d (cm)	
Accessories required	Chiller unit, Vacuum pump	
Weight	20 kg (Analyzer), 11 kg (Chiller unit), 9 kg (Vacuum pump)	20 kg (Analyzer), 11 kg (Chiller unit), 24 kg (Vacuum pump)
Power	100–240 VAC / 50–60 Hz; <100 W Analyzer, <230 W (Pump and Chiller unit)	100–240 VAC / 50–60 Hz; <100 W Analyzer, <450 W (Pump and Chiller unit)
Installation	19" Rack mountable or benchtop	
Digital Ports	RS232 (for data output), USB, Ethernet	
Connectivity	The instrument provides remote access and control of its main functionalities. It contains a PC which is running the instrument software. If a network access is provided, the instrument's full functionality can be accessed via a remote control software.	
Electrical and Laser Safety	CE-Mark (EN IEC 61326-1: 2021, EN IEC 61000-3-2: 2019, EN 61000-3-3:2013/ A2 :2021, EN 61010-1:2010/ AI:2019/AC:2019, EN 60825-1:2014/ All:2021/AC:2022, EN IEC 63000:2018)	
Service Interval	The instrument is suitable for operation without on-site interventions for a period of at least three weeks.	

Specifications

Species	MGA ¹⁰ - GP	MGA ⁵ - GHG	MGA ³ - GHG	Max. Drift* (24 hours)	Specification Range	Measurement Range (ppm)
	Precision @ 1s / <200 s	Precision @ 1s / <200 s	Precision @ 1s / <200 s			
CH ₄ (ppb)	1 (0.2)	1 (0.2)	0.3 (0.1)	5	1'000 - 3'000	0 - 200
CO (ppb)	0.4 (0.1)	0.4 (0.1)	0.1 (0.05)	1	0 - 1'000	0 - 20
CO ₂ ** (ppm)	0.5 (0.05)**	0.5 (0.05)	0.5 (0.05)	1	300 - 500	0 - 8'000
SO ₂ (ppb)	2 (0.2)	-	-	5	0 - 300	0 - 150
NH ₃ (ppb)	0.1 (0.02)	-	-	1	0 - 50	0 - 15
N ₂ O (ppb)	0.5 (0.05)	0.2 (0.07)	0.03 (0.01)**	2	300 - 400	0 - 20
NO (ppb)	0.8 (0.1)	-	-	2	0 - 400	0 - 100
NO ₂ (ppb)	0.4 (0.04)	-	-	1	0 - 200	0 - 40
H ₂ O (ppm)	20 (2)	30 (5)	10 (5)**	120	0 - 30'000	0 - 100'000
O ₃ (ppb)	1 (0.2)	-	-	10	0 - 300	0 - 300
OCS (ppb)	0.05 (0.01)	-	-	2	0 - 100	0 - 2
HONO (ppb)	2 (0.4)	-	-	10	0 - 300	0 - 5

* Maximum pk-to-pk difference of 1-hour averaged data over 24 hours. Drift for reactive species (SO₂, NO, NO₂, O₃) can be greatly improved by activating MIRO's automatic zero-air correction using scrubbed, clean air or nitrogen. ** Depending on the configuration these values might slightly differ.

Bruker Optics & MIRO Analytical are continually improving their products and reserves the right to change specifications without notice.
© 2023 Bruker Optics & MIRO Analytical BOPT-01

Bruker Optics GmbH & Co. KG
info.bopt.de@bruker.com

MIRO Analytical AG
support@miro-analytical.com

bruker.com



miro-analytical.com

